

MPX SERIES CONNECTOR



MPX Series couplings add ease of use and security to your most critical fluid handling applications. Choose from a full line of connectors and configurations, including pressure sealing caps and plugs in sizes to fit 3/8" and 1/2" tubing. MPX couplings offer optional locking sleeves to further guard against accidental disconnects. In addition, coupling halves can be rotated when connected reducing tube kinks.

FEATURES

- Ergonomic thumb latch
- USP Class VI materials
- Sterilizable by autoclave, EtO, e-beam, or gamma
- Parting line-free hose barb
- ADCF-free materials

BENEFITS

- Easy to operate – even with gloved hands
- Meet biocompatibility requirements
- Reusable, yet economical enough to allow disposability
- Eliminates potential leak path
- Meet BSE/TSE requirements



4040 Norex Drive, Chaska MN 55318
 phone: 952.448.4412 | fax: 952.448.6180
 sales@smithengineeringinc.com
 www.smithengineeringinc.com

Specifications ● ● ●

PRESSURE:

Vacuum to 60 psi, 4.1 bar

TEMPERATURE:

Polycarbonate:

-40°F to 250°F (-40°C to 121°C)

Polysulfone:

-40°F to 300°F (-40°C to 149°C)

MATERIALS:

Main components:

Polycarbonate (purple tint), USP Class VI, ADCF
 Polysulfone (amber tint), USP Class VI, ADCF

Locking sleeves:

Polysulfone (white), USP Class VI, ADCF

Thumb Latches:

Polycarbonate (white), USP Class VI, ADCF
 Polysulfone (amber tint), USP Class VI, ADCF

O-rings: Silicone (clear), platinum-cured, USP Class VI, ADCF

STERILIZATION:

Gamma: Up to 50 kGy irradiation

Autoclave:


Polycarbonate: Up to 250°F (121°C), 30 minutes, up to 10 repetitions. Sterilize uncoupled only.

Polysulfone: Up to 270°F (132°C) for 60 minutes, up to 25 repetitions. Sterilize uncoupled only.


TUBING SIZES: 3/8" to 1/2" ID (9.5mm to 12.7mm)

WARNING: Pressure, temperature, chemicals, and operating environment can affect the performance of couplings. It is the customer's responsibility to test the suitability of CPC's products in their own application conditions.

⚠ This graph is intended to give you a general idea of the performance capabilities of each product line. The shaded area of the graph represents the operating range of the product family, i.e. upper and lower values are shown. Therefore, depending on the exact coupling configurations selected, you can reasonably expect values to fall within the shaded area.



MPX SERIES CONNECTOR DIMENSIONS



A = Height/Diameter
B = Total Length

Coupling Bodies

• POLYCARBONATE

	TERMINATION IN-LINE HOSE BARB	TUBING 1/2" ID	METRIC EQ. 12.7mm ID	FLOW .50"	STRAIGHT THRU MPX17803	A 1.28 (32.5)	B 1.96 (49.8)
	IN-LINE HOSE BARB WITH LOCK	1/2" ID	12.7mm ID	.50"	MPXK17803	1.28 (32.5)	1.96 (49.8)

• POLYSULFONE

	TERMINATION IN-LINE HOSE BARB	TUBING 1/2" ID	METRIC EQ. 12.7mm ID	FLOW .50"	STRAIGHT THRU MPX17839	A 1.28 (32.5)	B 1.96 (49.8)
	IN-LINE HOSE BARB WITH LOCK	1/2" ID	12.7mm ID	.50"	MPXK17839	1.28 (32.5)	1.96 (49.8)

Coupling Inserts

• POLYCARBONATE

	TERMINATION IN-LINE HOSE BARB	TUBING 3/8" ID	METRIC EQ. 9.5mm ID	FLOW .38"	STRAIGHT THRU MPX22603M	O-RING Silicone Seal USP Class VI	A .85 (21.6)	B 1.90 (48.3)
		1/2" ID	12.7mm ID	.50"	MPX22803M	Silicone Seal USP Class VI	.85 (21.6)	1.90 (48.3)

• POLYSULFONE

	TERMINATION IN-LINE HOSE BARB	TUBING 3/8" ID	METRIC EQ. 9.5mm ID	FLOW .38"	STRAIGHT THRU MPX22639M	O-RING Silicone Seal USP Class VI	A .85 (21.6)	B 1.90 (48.3)
		1/2" ID	12.7mm ID	.50"	MPX22839M	Silicone Seal USP Class VI	.85 (21.6)	1.90 (48.3)

Mating Parts

	SEALING CAP MPX32003	SEALING CAP W/LOCK MPXK32003	MATERIAL Polycarbonate	A 1.28 (32.5)	B 1.67 (42.4)
	MPX32039	MPXK32039	Polysulfone	1.28 (32.5)	1.67 (42.4)

	SEALING PLUG MPX30003M	O-RING Silicone Seal USP Class VI	MATERIAL Polycarbonate	A 1.10 (27.9)	B 1.66 (42.2)
	MPX30039M	Silicone Seal USP Class VI	Polysulfone	1.10 (27.9)	1.66 (42.2)

Note:
 MPX Series
 mates with Back-to-
 Back Adapters (page
 109), SaniQuik™ and
 Sanitary Series
 (pages 112-115).

All measurements are in inches (millimeters) unless otherwise noted. Tubing must meet stated inside and outside diameters.